

# Instructions for AC-IR Power Switch

The AC-AUD features a single switched outlet that is capable of 1800 watts maximum continuous current. The outlet is normally off until a trigger signal is detected. The AC-IR can teach learning remotes the IR codes.

To teach the ON command, hold the learning remote in front of the teaching LED next to the AC outlet and press the RED button located on the side of the unit. This will teach the ON command to the remote and also turn the AC-IR on.

To teach the OFF command, hold the learning remote in front of the teaching LED next to the AC outlet and press the BLACK button located on the side of the unit. This will teach the OFF command to the remote and also turn the AC-IR off.

The AC-IR features a relay to switch the power to the outlet. This allows the AC-IR to be used with high current equipment such as amplifiers. The AC-IR does not include surge protection or line filtering. If these are required, use an independent surge arrester commonly available.

clear blue  audio video

**Clear Blue Audio Video**  
6040 W. 91st Ave.  
Westminster, CO 80031  
phone 800-869-5632 fax 888-869-5632  
[www.cbav.com](http://www.cbav.com)